



Somos® Evolve 128

An durable stereolithography (SLA) material that creates parts ready for functional testing.

Product Description

Somos® EvoLve 128 is a durable stereolithography material that produces accurate, high-detailed parts and has been designed for easy finishing. It has a look and feel that is almost indistinguishable from finished traditional thermoplastics, making it excellent for building parts and prototypes for functional testing applications – resulting in time, money and material savings during product development. Somos® EvoLve is an excellent material for industries such as aerospace, automotive, medical, consumer products and electronics.

Key Benefits

- Easy to clean & finish
- High strength and durability
- Accurate & dimensionally stable
- High detail

Ideal Applications

- Tough, functional prototypes
- Snap-fit designs
- Jigs & fixtures

Somos[®] Evolve 128 Technical Data

Liquid Properties			
Appearance		Off-White	
Mechanical Properties		UV Postcure	
ASTM Method	Property Description	Metric	Imperial
D638M	Tensile Modulus	2,964 MPa	430 ksi
D638M	Tensile Strength at Yield	56.8 MPa	8.2 ksi
D638M	Elongation at Break	11%	
D2240	Flexural Modulus	2,654 MPa	385 ksi
D256A	Izod Impact (notched)	38.9 J/m	0.729 ft-lb/in
D2240	Hardness (Shore D)	82	
D570-98	Water Absorption	0.4 %	

Thermal/Electrical Properties		UV Postcure	
ASTM Method	Property Description	Metric	Imperial
E831-05	C.T.E. -40—0°C (-40– 32°F)	56.5 µm/m°C	31.4 µin/in°F
E831-05	C.T.E. 0—50°C (32– 122°F)	76.5 µm/m°C	42.5 µin/in°F
E831-05	C.T.E. 50—100°C (122– 212°F)	163 µm/m°C	90.8 µin/in°F
E831-05	C.T.E. 100—150°C (212– 302°F)	174 µm/m°C	96.5 µin/in°F
D150-98	Dielectric Constant 60 Hz	4.3	
D150-98	Dielectric Constant 1 KHz	3.7	
D150-98	Dielectric Constant 1 MHz	3.5	
D149-97a	Dielectric Strength	31 kV/mm	788 V/mil
D648	HDT @ 0.46 MPa (66 psi)	52.3°C	126°F
D648	HDT @ 1.81 MPa (264 psi)	49.6°C	121°F

PERIDOT INC
 14508 Bruick Drive
 Hoagland, IN 46745



PH: 260.639.6500
 FX: 260.639.6503
www.peridotinc.com